

ABC calibration sheets

Please note: When printing the calibration sheets A, B and C, you have to choose actual size and not scale to fit page in print settings.

If you do not print in actual size the performed measurements will not be correct.

On page 5, you can find a metric and imperial ruler to verify the accuracy of your calibration.

TAGARNO




Range to cover: 204 ~ 340 mm

Dot diameter: 6.809 mm

Spacing: 16.681 mm


Number dots X: 17

Number dots Y: 10






Range to cover: 123 – 204 mm
Dot diameter: 4.085 mm
Spacing: 10.009 mm
Number dots X: 20
Number dots Y: 11






Range to cover: 74 – 123 mm
Dot diameter: 2.451 mm
Spacing: 6.005 mm
Number dots X: 20
Number dots Y: 11



15 cm ruler

Verify calibration when using metric system units



6 inch ruler

Verify calibration when using imperial system units

